



ROHS



REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:
Voltage Rating: 250V
Current Rating: 3AMP
Temperature Range: -40°C to $+105^{\circ}\text{C}$
Contact Resistance: $20\text{m}\Omega$ Max
Insulation Resistance: $1000\text{M}\Omega$ Min
Withstanding Voltage: AC 1000V
Material:
Insulator: Polyester (UL94V-0)
Standard: PA6T
Contact: Brass
Plating: Au over Ni



COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
DRAWING							
CHECKED							
APPROVED							
TOLERANCES ARE			TITLE		排针 PIN距2.54 塑高2.5 双排6PIN立贴	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-PZ2.54-6PX2-T	UNITS	mm	
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
			DWG. NO.			Projection	