





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:
Current Rating: 3AMP
Temperature Range: -40°C~+105°C
Contact Resistance: 20mΩ Max
Insulation Resistance: 1000MΩ Min
Withstanding Voltage: AC 1000V
Material:
Insulator: Polyester (UL94V-0)
Standard: PA9T
Contact: Brass
Plating: Au over Ni



PCB LAYOUT

CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD			
DRAWING		TITLE 排母 PIN距2.54 塑高8.5 单排9PIN直针 REV. A			
CHECKED					
APPROVED					
TOLERANCES ARE		PART NO.	LAIL-PM2. 54-9P-L	UNITS	mm
30-150	±0.35				
10-30	±0.2	DWG. NO.		Projection	
5-10	±0.15				
0-5	±0.1				