









P . C . B LAYOUT



CIRCUIT DIAGRAM

Operating force	model selection
100gf±30gf	
160gf±40gf	
260gf±50gf	

NO.	NAME	MATERIAL	QTY	REMARK
1	TERMINAL	C5191	1	Ag plating(0.2 μm min)
2	CASE	LCP	1	white
3	CONTACT	SUS301	1	Ag plating(0.3 μm min)
4	DUSTPROOF FILM	PI	1	Yellow

SPECIFICATIONS	
Operating temperature ranges	-30° to +85°
Rating	DC 12V 50mA Max.
Contact Resistance	100mΩ Max
Dielectric strength	250V AC for 1min.
insulation resistance	100mΩ Min. 100V DC
Travel	0.15±0.05mm
Operating Life (cycles)	50 000 CYCLES

 安泰珂电子有限公司 Antenk Electronics Co.,Ltd		PART NO ; 4.8*4.8*0.55H	
.X: ±0.25	X° : ±8°	 CUSTOMER ITEM NO	
.XX: ±0.15	.X° : ±5°		
.XXX: ±0.05	.XX° : ±2°		
APPD	Wu Jianzhen	SCALE: 1:1	
CHKD	Zheng Maowei		
DRAW	Li San qiang	REV; AO	UNIT; MM
		PAGE ; 1-1	