





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:
Voltage Rating: 250V
Current Rating: 3AMP
Temperature Range: -40℃to+105℃
Contact Resistance: 20mΩ Max
Insulation Resistance: 1000MΩ Min
Withstanding Voltage: AC 1000V
Material:
Insulator: Polyester (UL94V-0)
Standard: PA6T
Contact: Brass
Plating: Au over Ni



PCB LAYOUT General±0.05mm.

CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD						
DRAWING		TITLE 排针 PIN距2.54 塑高2.5 单排10PIN直插		REV.	A			
CHECKED								
APPROVED								
TOLERANCES ARE		PART NO. LAIL-PZ2.54-10P-L	UNITS mm	DWG. NO.	Projection 			
30-150	±0.35							
10-30	±0.2							
5-10	±0.15							
0-5	±0.1							
ANGLE								
		±3°						