





2x03-2x08P

P. C. B. LAYOUT




2x02P

P. C. B. LAYOUT



2x01P

P. C. B. LAYOUT



SPECIFICATIONS (规格)

- Voltage Rating (额定电压) : 250V AC, DC
- Current Rating (额定电流) : 7A, AC, DC
- Withstanding Voltage (耐电压) 1500V AC/minute
- Insulation Resistance (绝缘电阻) :1000M Ω min
- Temperature Range (工作温度) -25° C~+85° C
- Contact Resistance (接触电阻) : 10m Ω max
- Material:
- Insulator: Nylon 66 UL94V-2
- Pin Material: Brass /Tin-Plated

Poles	PART NO.	Dimensions (mm)	
		A	B
2x01P	W-5557R02P-D000	—	5.40
2x02P	W-5557R04P-D000	4.20	9.60
2x03P	W-5557R06P-D000	8.40	13.80
2x04P	W-5557R08P-D000	12.60	18.00
2x05P	W-5557R10P-D000	16.80	22.20
2x06P	W-5557R12P-D000	21.00	26.40
2x07P	W-5557R14P-D000	25.20	30.60
2x08P	W-5557R16P-D000	29.40	34.80
2x09P	W-5557R18P-D000	33.60	39.00
2x10P	W-5557R20P-D000	37.80	43.20
2x11P	W-5557R22P-D000	42.00	47.40
2x12P	W-5557R24P-D000	46.20	51.60

TOLERANCE TABLE

.0	±0.30
.00	±0.15
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: 5557R-2*1P 带定位柱			
DRAWN: LYF	DATE: 2024-10-31	CLIENT P/N		W-5557RXXP-D000	
		UNIT	mm	SCALE	free
		FILE NO.		Ckmtw-5557-0020	REV. A