




ROHS



PCB LAYOUT

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Current Rating: 3AMP

Temperature Range: -40°C~+105°C

Contact Resistance: 20mΩ Max

Insulation Resistance: 1000MΩ Min

Withstanding Voltage: AC 1000


Material:

Insulator: Polyester(UL94V-0)

Standard: PA9T

Contact: Brass

Plating: Au over Ni



COSTOMER DRAWING			LAILAN 深圳市莱联电子有限公司			
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECKED						
APPROVED						
TOLERANCES ARE			TITLE	排母 PIN距2.54 塑高8.5 双排5PIN立贴	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-PM2.54-5PX2-T	UNITS	mm
10-30	±0.2		DWG. NO.		Projection	
5-10	±0.15					
0-5	±0.1					