




规格说明:Specifications:

电气特性:Electrical:

1. 额定电流: Current Rating
1.0A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗: Contact Resistance
50 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:
300 V AC For one minute
5. 绝缘阻抗: Insulation Resistance:
100MEGA ohms MIN


原材料:Raw material:

1. 塑胶: Plastic cement:
Hing Temperature Thermoplastics,
LCP Black
2. 端子: Contact: Copper Alloy C5191
3. 外壳: Shell: Copper Alloy C2680

电镀: Electroplate:

1. 端子: Contact: Plated Gold in Mating Area;
2. 外壳: Shell:
Nickel Plating

2A-2外壳
1A-2端子



 深圳市宇文发电子科技有限公司 Shen Zhen Yu Wen Fa Electronics Technology Co., Ltd TEL: 0755-27711235 FAX: 0755-27712683		页码 (SHEET)	1/1	单位 (UNIT): MM
品名 (ITEM NO)		版本 (REV)	A0	比例 (SCALE) 1:1
料号 (PART NO)		日期 (DATE)	2018.08.21	
图号 (DWG NO)		设计 (DESIGN)	Lee	未注公差 TOLERANCE UNSPECIFIED
		审核 (CHECKED)		X.X ±0.30
		核准 (APPROVED)		X.XX ±0.20
				X.XXX ±0.10
				X° ±5°
				X.X° ±2°

RoHS Compliant




REV.	ECN NO	DESCRIPTION	REVISER	DATE
A/0				
A/1				




① 胶盘




② 1000pcs/盘



③ 10盘/箱 (10 Kpcs)





④ 每箱装10盘, 若尾数箱在空间处加装填充物.




⑥ 依图示粘贴产品或ROHS标签.

外箱物料标签




⑤ 外箱用透明胶纸带封“工”字型.



备注:

1. 胶盘规格: 330*16mm
2. 每盘装1.0K pcs;
3. 每箱装10盘 (10K pcs);
4. 外箱尺寸: 长*宽*高: 34*34*32cm;
5. 外箱用透明胶纸带封“工”字型;
6. 依外箱图示位置粘贴好产品或ROHS标签.

图号 (DWG NO)		单位 (UNIT): MM	 深圳宇文发电子科技有限公司 TEL:0755-27711235 FAX:0755-27712683	
日期 (DATE)	2012. 06. 27	比例 (SCALE) 1:1		
版次 (REV): A/0	页/次(PAGE): 1/1			
设计 (DESIGN)	李丰桔	包装规范	品名 (ITEM NO)	MICRO USB 5P/F 卷装系列(1000PCS/盘)
审核 (CHECKED)	吴华兴		料号 (PART NO)	
核准 (APPROVED)				