




规格说明:Specifications:

电气特性:Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗:Contact Resistance
30 milliohms MAX
4. 耐电压:Dielectric Withstanding Voltage:
500 V AC For one minute
5. 绝缘阻抗:Insulation Resistance:
1000MEGA ohms MIN

原材料:Raw material:

1. 塑胶:Plastic cement:
Hing Temperature Thermoplastics,
PBT/LCP White/ Black
2. 端子>Contact:Copper Alloy C2680/C5191
3. 外壳:Shell: SPCC/Copper Alloy C2680

电镀:Electroplate:


1. 端子>Contact: Plated Gold in Mating Area;
Tin On Solder Talls
2. 外壳:Shell:
Nickel Plating

1B外壳
1B-1端子


深圳市宇文发电子科技有限公司 Shen Zhen Yu Wen Fa Electronics Technology Co.,Ltd TEL:0755-27711235 FAX:0755-27712683		页码 (SHEET)	1/1	单位(UNIT): MM
		版本 (REV)	A0	比例(SCALE) 1:1
		日期 (DATE)	2009. 12. 17	未注公差 TOLERANCE UNSPECIFIED
		设计 (DESIGN)	陈钦虎	X. X ±0.30 X. XX ±0.20 X. XXX ±0.10 X° ±5° X. X° ±2°
		审核 (CHECKED)		
品名 (ITEM NO)	USB A/F 180° 焊线	核准 (APPROVED)		
料号 (PART NO)	PUBFA-R15A-001			
图号 (DWG NO)	P-UBF-104 (1B)			

RoHS Compliant


REV.	ECN NO	DESCRIPTION	REVISER	DATE
A/0				
A/1				




① PE袋.




② 1000Pcs/袋, 并用封口机封口.




③ 5袋/箱 (5k).



⑥ 依图示粘贴产品或ROHS标签.




⑤ 外箱用透明胶纸带封“工”字型.



④ 每箱平放5袋, 若尾数箱在空间处加装填充物.

备注:

1. PE袋.
2. 每袋装成品1000Pcs, 并用封口机封口;
3. 每箱装5袋 (5KPcs);
4. 外箱尺寸43.5*27.5*18cm ;
5. 外箱用透明胶纸带封“工”字型;
6. 依外箱图示位置粘贴好产品或ROHS标签.

图号 (DWG NO)		单位 (UNIT): MM	 深圳宇文发电子科技有限公司 TEL:0755-27711235 FAX:0755-27712683	
日期 (DATE)	2011/11/24	比例 (SCALE) 1:1		
版次 (REV): A/0	页/次(PAGE): 1/1			
设计 (DESIGN)	Gavin Deng	包装规范	品名 (ITEM NO)	USB AF 180度 焊线式系列
审核 (CHECKED)			料号 (PART NO)	
核准 (APPROVED)	Toms Chen			