




ROHS



PCB LAYOUT General±0.05mm.

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Voltage Rating: 250V

Current Rating: 3AMP

Temperature Range: -40℃to+105℃

Contact Resistance: 20mΩ Max

Insulation Resistance: 1000MΩ Min

Withstanding Voltage: AC 1000V


Material:

Insulator: Polyester (UL94V-0)

Standard: PA6T

Contact: Brass

Plating: Au over Ni



CUSTOMER DRAWING				LAILAN 深圳市莱联电子有限公司			
DRAWING				SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECKED							
APPROVED							
TOLERANCES ARE				TITLE	排针 PIN距2.54 塑高2.5 双排4PIN直针	REV.	A
30-150	±0.35	ANGLE	±3°	PART NO.	LAIL-PZ2. 54-4PX2-L	UNITS	mm
10-30	±0.2			DWG. NO.		Projection	
5-10	±0.15						
0-5	±0.1						