





ROHS



PCB LAYOUT

SPECIFICATION:

Voltage Rating: AC 250V

Current Ratin : 1AMP

Temperature Range: -40°C~+105°C

Contact Resistance: 20mΩ Max

Insulation Resistance: 1000MΩ Min

Withstanding Voltage: AC 500V

Material:

Insulator: Polyester (UL94V-0)

Standard: PA9T

Contact: C5159

Plating: Au over Ni

|                  |       |       |                                       |                            |            |    |
|------------------|-------|-------|---------------------------------------|----------------------------|------------|----|
| CUSTOMER DRAWING |       |       | LAILIAN 深圳市莱联电子有限公司                   |                            |            |    |
| DRAWING          |       |       | SHENZHEN LAILIAN ELECTRONICS CO., LTD |                            |            |    |
| CHECKED          |       |       |                                       |                            |            |    |
| APPROVED         |       |       |                                       |                            |            |    |
| TOLERANCES ARE   |       |       | TITLE                                 | 排母 PIN距1.27 塑高4.3 双排4PIN立贴 | REV.       | A  |
| 30-150           | ±0.35 | ANGLE | PART NO.                              | LAIL-PM1.27-4PX2-T         | UNITS      | mm |
| 10-30            | ±0.2  |       | DWG. NO.                              |                            | Projection |    |
| 5-10             | ±0.15 |       |                                       |                            |            |    |
| 0-5              | ±0.1  |       |                                       |                            |            |    |