


ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:
Voltage Rating: 250V
Current Rating: 2AMP
Temperature Range: -40℃to+105℃
Contact Resistance: 20mΩ Max
Insulation Resistance: 1000MΩ Min
Withstanding Voltage: AC 500V
Material:
Insulator: Polyester (UL94V-0)
Standard: PA6T
Contact: Brass
Plating: Au over Ni



PCB LAYOUT General±0.05mm.

COSTOMER DRAWING			LAILAN 深圳市莱联电子有限公司			
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
CHECKED						
APPROVED						
TOLERANCES ARE			TITLE	排针 PIN距2.0 塑高2.0 单排4PIN直插	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-PZ2.0-4P-L	UNITS	mm
10-30	±0.2		DWG. NO.		Projection	
5-10	±0.15					
0-5	±0.1					