




ROHS



PCB LAYOUT General±0.05mm.

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Voltage Rating: 250V

Current Rating: 3AMP

Temperature Range: -40°Cto+105°C

Contact Resistance: 20mΩ Max

Insulation Resistance: 1000MΩ Min

Withstanding Voltage: AC 1000V


Material:

Insulator: Polyester (UL94V-0)

Standard: PA6T

Contact: Brass

Plating: Au over Ni



COSTOMER DRAWING			LAILAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING			TITLE 排针 PIN距2.54 塑高2.5 单排2PIN直插			
CHECKED						
APPROVED						
TOLERANCES ARE			REV. A			
30-150	±0.35	ANGLE	PART NO. LAIL-PZ2.54-2P-L		UNITS mm	
10-30	±0.2					
5-10	±0.15					
0-5	±0.1	±3°	DWG. NO.		Projection 	