





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:
Voltage Rating: 250V
Current Rating: 2AMP
Temperature Range: -40℃to+105℃
Contact Resistance: 20mΩ Max
Insulation Resistance: 1000MΩ Min
Withstanding Voltage: AC 500V
Material:
Insulator: Polyester (UL94V-0)
Standard: PA6T
Contact: Brass
Plating: Au over Ni



PCB LAYOUT General±0.05mm.

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING					
CHECKED					
APPROVED					
TOLERANCES ARE		TITLE	排针 PIN距2.0 塑高2.0 单排2PIN直插	REV.	A
30-150	±0.35	PART NO.	LAIL-PZ2. 0-2P-L	UNITS	mm
10-30	±0.2				
5-10	±0.15	DWG. NO.		Projection	
0-5	±0.1				
ANGLE					
±3°					