



REV. (版本号)	DESCRIPTION (变更说明)	DATE (日期)	APPD (核准)
A0	新订图面	2019. 02. 19	Lee



3D VIEW

NOTES:

1.MATERIAL:SEE TABLE

2.PLATING:SEE TABLE

3.ELECTRICAL PERFORMANCE:

CONTACT RESISTANCE:INITIAL CONTACT RESISTANCE

EXCLUDING CONDUCTOR RESISTANCE:10 MILLIOHMS MAX




DIELECTRIC STRENGTH:UNMATED CONNCTORS APPLY 500V AC

MATED CONNECTOR APPLY 300V AC

INSULATION RESISTANCE:100 MEGAOHMS MIN.(UNMATED)

10 MEGAOHMS MIN.(MATED)


4.All MATERIALS NEED TO MEET ROHS2 + HF
ENVIRONMENTAL AND SAFETY REQUIREMENTS



RECOMMENDED PCB LAYOUT THICKNESS=1.6mm
TOP VIEW;TOLERANCE=±0.05


TABLE:

NO	PART	Q'TY	Material
1	SHELL	1	STAINLESS STEEL T=0.4mm,Ni PLATED 50u"Min
2	TERMINAL	19	COPPER ALLOY T=0.2mm,NI 50u"Min;Au G/F;Au u"
3	HOUSING	1	LCP UL 94V-0 BLACK
4	COVER	1	LCP UL 94V-0 BLACK




 深圳市宇文发电子科技有限公司 Shen Zhen Yu Wen Fa Electronics Technology Co.,Ltd TEL:0755-27711235 FAX:0755-27712683		页码 (SHEET)	1/1	单位(UNIT): MM
品名 (ITEM NO)	HDMI A TYPE 19P H=15.10 REC V/T DIP TYPE(BSB-2)	版本 (REV)	A0	比例(SCALE) 1:1
料号 (PART NO)	PHDFA-R12A-001	日期 (DATE)	2019. 02. 19	 未注公差 TOLERANCE UNSPECIFIED X.X ±0.30 X.XX ±0.20 X.XXX ±0.10 X° ±5° X.X° ±2°
图号 (DWG NO)	P-HDF-001	设计 (DESIGN)	Lee	
		审核 (CHECKED)		
		核准 (APPROVED)		

RoHS Compliant


REV.	ECN NO	DESCRIPTION	REVISER	DATE
A/0				
A/1				




① 胶盘



② 200pcs/盘




③ 6盘/箱 (1.2 Kpcs)




⑥ 依图示粘贴产品或ROHS标签.

外箱物料标签




⑤ 外箱用透明胶纸带封“工”字型.



④ 每箱装6盘, 若尾数箱在空间处加装填充物.

备注:

1. 胶盘规格: 380*45mm
2. 每盘装0.2K pcs;
3. 每箱装6盘 (1.2K pcs);
4. 外箱尺寸: 长*宽*高: 39.5*39.5*31cm;
5. 外箱用透明胶纸带封“工”字型;
6. 依外箱图示位置粘贴好产品或ROHS标签.

图号 (DWG NO)		单位 (UNIT): MM	 深圳市宇文发电子科技有限公司 Shen Zhen Yu Wen Fa Electronics Technology Co., Ltd TEL: 0755-27711235 FAX: 0755-27712683	
日期 (DATE)	2019. 05. 30	比例 (SCALE) 1:1		
版次 (REV): A/0	页/次 (PAGE): 1/1			
设计 (DESIGN)	Lee	包装规范	品名 (ITEM NO)	HDMI A TYPE 19P 卷装系列
审核 (CHECKED)			料号 (PART NO)	
核准 (APPROVED)				