


ROHS



REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Voltage Rating: 250V

Current Rating: 3AMP

Temperature Range: -40°C to $+105^{\circ}\text{C}$

Contact Resistance: $20\text{m}\Omega$ Max

Insulation Resistance: $1000\text{M}\Omega$ Min

Withstanding Voltage: AC 1000V

Material:

Insulator: Polyester (UL94V-0)

Standard: PA6T

Contact: Brass

Plating: Au over Ni

COSTOMTER DRAWING			LAILIAN 深圳市莱联电子有限公司					
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD					
CHECKED								
APPROVED								
TOLERANCES ARE			TITLE		排针 PIN距2.54 塑高2.5 双排5PIN立贴	REV.	A	
30-150	±0.35	ANGLE	PART NO.	LAIL-PZ2.54-5PX2-T	UNITS	mm		
10-30	±0.2							
5-10	±0.15							
0-5	±0.1							
			DWG. NO.				Projection	