





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:
Current Rating: 3AMP
Temperature Range: -40°C~+105°C
Contact Resistance: 20mΩ Max
Insulation Resistance: 1000MΩ Min
Withstanding Voltage: AC 1000V
Material:
Insulator: Polyester (UL94V-0)
Standard: PA9T
Contact: Brass
Plating: Au over Ni



PCB LAYOUT

CUSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
DRAWING							
CHECKED							
APPROVED							
TOLERANCES ARE			TITLE		排母 PIN距2.54 塑高8.5 双排10PIN弯针	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-PM2.54-10PX2-W	UNITS	mm	
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
			±3°	DWG. NO.		Projection	