


ROHS

| REV. | ECN NO. | DESCRIPTION | DRAW | DATE |
|------|---------|-------------|------|------|
|      |         |             |      |      |

SPECIFICATION:  
Current Rating: 3AMP  
Temperature Range: -40°C~+105°C  
Contact Resistance: 20mΩ Max  
Insulation Resistance: 1000MΩ Min  
Withstanding Voltage: AC 1000V  
Material:  
Insulator: Polyester (UL94V-0)  
Standard: PA9T  
Contact: Brass  
Plating: Au over Ni



|                  |       |                                                              |             |            |                                                                                       |              |
|------------------|-------|--------------------------------------------------------------|-------------|------------|---------------------------------------------------------------------------------------|--------------|
| CUSTOMER DRAWING |       | LAILIAN 深圳市莱联电子有限公司<br>SHENZHEN LAILIAN ELECTRONICS CO., LTD |             |            |                                                                                       |              |
| DRAWING          |       | TITLE<br>排母 PIN距2.54 塑高8.5 单排5PIN直针                          |             | REV.       | A                                                                                     |              |
| CHECKED          |       |                                                              |             |            |                                                                                       |              |
| APPROVED         |       |                                                              |             |            |                                                                                       |              |
| TOLERANCES ARE   |       | PART NO.<br>LAIL-PM2.54-5P-L                                 | UNITS<br>mm | Projection |  |              |
| 30-150           | ±0.35 |                                                              |             |            |                                                                                       | ANGLE<br>±3° |
| 10-30            | ±0.2  |                                                              |             |            |                                                                                       |              |
| 5-10             | ±0.15 |                                                              |             |            |                                                                                       |              |
| 0-5              | ±0.1  |                                                              |             |            |                                                                                       |              |
|                  |       | DWG. NO.                                                     |             |            |                                                                                       |              |