




ROHS



PCB LAYOUT

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Current Rating: 3AMP

Temperature Range: -40°C~+105°C

Contact Resistance: 20mΩ Max

Insulation Resistance: 1000MΩ Min

Withstanding Voltage: AC 1000


Material:

Insulator: Polyester(UL94V-0)

Standard: PA9T

Contact: Brass

Plating: Au over Ni



COSTOMTER DRAWING			 深圳市莱联电子有限公司				
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD				
CHECKED							
APPROVED							
TOLERANCES ARE			TITLE		排母 PIN距2.54 塑高8.5 双排8PIN立贴	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-PM2.54-8PX2-T	UNITS	mm	
10-30	±0.2		DWG. NO.		Projection 		
5-10	±0.15						
0-5	±0.1						