









REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




序号	品名	材质
1	基座	LCP UL94V-0 本色
2	端子	磷青铜/表面镀锡



技术指标:

1. 额定电流: 0.5A
2. 温度范围: -40~85℃
3. 额定电压: 50V, AC/DC (等效)
4. 接触电阻: ≤0.03Ω
5. 绝缘电阻: ≥500MΩ

Part No	Pin	A	B	C
JXT-A10FC-S4FLZ-H47	4	3.00	5.10	6.00
JXT-A10FC-S5FLZ-H47	5	4.00	6.10	7.00
JXT-A10FC-S6FLZ-H47	6	5.00	7.10	8.00
JXT-A10FC-S7FLZ-H47	7	6.00	8.10	9.00
JXT-A10FC-S8FLZ-H47	8	7.00	9.10	10.00
JXT-A10FC-S9FLZ-H47	9	8.00	10.10	11.00
JXT-A10FC-S10FLZ-H47	10	9.00	11.10	12.00
JXT-A10FC-S11FLZ-H47	11	10.00	12.10	13.00
JXT-A10FC-S12FLZ-H47	12	11.00	13.10	14.00
.....		...		
JXT-A10FC-S36FLZ-H47	36	(36-1)*1.0	(36+1)*1.0+0.10	38.00

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.15	±1°	PART NO.	TITLE:		
X.X±0.10		JXT-A10FC-SNFLZ-H47	1.0B黑色双面接立式 (正位)		
X.XX±0.05		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	— — —	APPD: Ava		N:A	1/1