







SPECIFICATIONS

Current Rating:0.75 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000MΩ Min
Contact Resistance:20mΩ Max
Operation Temperature:−40°to+105°
Insrlator Material:Polyester(UL94V-0)
Contact Material:Phosphor bronze
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp:
240°C for30-60seconds
(260°C for5seconds)



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

P/N	PIN	DIM.A	DIM.B
JXT-PZ1.0-1X1P-A1	1	0.00	1.00
JXT-PZ1.0-1X2P-A1	2	1.00	2.00
JXT-PZ1.0-1X3P-A1	3	2.00	3.00
JXT-PZ1.0-1X4P-A1	4	3.00	4.00
JXT-PZ1.0-1X5P-A1	5	4.00	5.00
JXT-PZ1.0-1X6P-A1	6	5.00	6.00
JXT-PZ1.0-1X7P-A1	7	6.00	7.00
JXT-PZ1.0-1X8P-A1	8	7.00	8.00
JXT-PZ1.0-1X9P-A1	9	8.00	9.00
.....			
JXT-PZ1.0-1X50P-A1	50	(50-1)	50



RECOMMEND P.C.B LAYOUT

PCB TOLERANCE:±0.05 (TOP VIEW)

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X ±0.30	X.* ±5°	PART NO.	TITLE:1.0PH H1.0 1xnPin 180度	
.XX ±0.20	X.X* ±1°	JXT-PZ1.0-1XNP-A1	W1.5 PC2.0 PA2.0 PB1.0 L5.0	
.XXX ±0.10	X.XX*±0.5°	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		SCALE
MATERILA	---	APPD: Ava		SHEET
FINISH	---			N:A
				1/1