








REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



- NOTE:
- MATERIAL SPECIFICATION:
 - HOUSING:HIGH TEMPERATURE RESISTANT PLASTIC,UL94 V-0 (PA9T)
 - TERMINAL: COPPER ALLOY (C18150)
 - MID PLATE: STAINLESS STEEL (SUS301)
 - FRONT SHELL: STAINLESS STEEL (SUS304)
 - EMI PLATE: STAINLESS STEEL (SUS304)
 - PLATING SPECIFICATION:
 - TERMINAL:

Ni 50u" MIN. UNDER PLATED OVER ALL.

Au PLATED ON THE FUNCTIONAL AREA OF CONTACT.

(GOLD PLATING THICKNESS Au 3u")

SN PLATING THE SOLDER AREA.
 - FRONT SHELL:

Ni 30u" MIN. UNDER PLATED OVER ALL.
 - MID PLATE&EMI PLATE:

CLEAR ONLY
 - MECHANICAL PERFORMANCE,
 - INSERTION FORCE: 0.5~2.0kgf.
 - REMOVAL FORCE: 0.8kgf~2.0kgf.
 - DURABILITY: 10000 CYCLES.
 - ELECTRICAL PERFORMANCE,
 - VOLTAGE RATING: 5V.
 - CURRENT RATING: 5A.
 - LLCR:

VBUS & GND PINS AND OTHER PINS: 40mA/PIN MAX.




LLCR MAX. CHANGE OF ALL PINS: 10mA.
 - INSULATION RESISTANCE: 100MΩ MIN
 - DIELECTRIC WITHSTAND VOLTAGE,AC 100V FOR 1 MINUTE.
 - ENVIRONMENTAL PERFORMANCE:

OPERATING TEMPERATURE: -40°C~+85°C.
 - IR REFLOW:

THE PEAK TEMPERATURE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 260°C.

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
.X±0.30	X.*±10°	PART NO.	TITLE:	
.XX±0.20	X.X*±8°	JXT-TYPE-C-G288H-24P	USB CF VERTICAL(L=8.8)	
.XXX±0.10	X.XX*±5°	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia	SCALE N:A	SHEET 1/3
MATERILA	---	APPD: Ava		
FINISH	---			

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN






USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A2	TXp1	B11	RXp1
A3	TXn1	B10	RXn1
A4	VBus	B9	VBus
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBus	B4	VBus
A10	RXn2	B3	TXn2
A11	RXp2	B2	TXp2
A12	GND	B1	GND

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd	
.X±0.30	X.*±10°	PART NO.	TITLE:
.XX±0.20	X.X*±8°	JXT-TYPE-C-G288H-24P	USB CF VERTICAL(L=8.8)
.XXX±0.10	X.XX*±5°	DESIGN: Ethan	MANUFACTURE DWG
UNITS	mm	CHED: Olvia	
MATERILA	---	APPD: Ava	
FINISH	---		SCALE N:A
			SHEET 2/3

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



		REEL/TRAY	CARTON
CONNECTOR (PCS)		450	4500
TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd	
.X $\pm$ 0.30	X.* $\pm$ 10"	PART NO.	TITLE:
.XX $\pm$ 0.20	X.X* $\pm$ 8"	JXT-TYPE-C-G288H-24P	USB CF VERTICAL(L=8.8)
.XXX $\pm$ 0.10	X.XX* $\pm$ 5"	DESIGN: Ethan	MANUFACTURE DWG
UNITS	mm	CHED: Olvia	SCALE N:A SHEET 3/3
MATERILA	---	APPD: Ava	
FINISH	---		