




SPECIFICATIONS

Current Rating:0.75 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000MΩ Min
Contact Resistance:20mΩ Max
Operation Temperature:−40°to+105°
Insrlator Material:Polyester(UL94V-0)
Contact Material:Phosphor bronze
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp:
240°C for30–60seconds
(260°C for5seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

P/N	PIN	DIM.A	DIM.B
JXT-PM1.0-1X1P-A3	1	0.00	1.00
JXT-PM1.0-1X2P-A3	2	1.00	2.00
JXT-PM1.0-1X3P-A3	3	2.00	3.00
JXT-PM1.0-1X4P-A3	4	3.00	4.00
JXT-PM1.0-1X5P-A3	5	4.00	5.00
JXT-PM1.0-1X6P-A3	6	5.00	6.00
JXT-PM1.0-1X7P-A3	7	6.00	7.00
JXT-PM1.0-1X8P-A3	8	7.00	8.00
JXT-PM1.0-1X9P-A3	9	8.00	9.00
.....			
JXT-PM1.0-1X40P-A3	40	(40-1)	40

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd	
X.X ±0.30	X.° ±5°	PART NO.	TITLE:1.0FH H2.0 1xnPin SMT
.XX ±0.20	X.X° ±1°	JXT-PM1.0-1XNP-A3	W1.5 U型 PC2.8 PB2.3 6T (左端后)
.XXX ±0.10	X.XX° ±0.5°	DESIGN: Ethan	MANUFACTURE DWG
UNITS	mm	CHED: Olvia	SCALE
MATERILA	---	APPD: Ava	SHEET
FINISH	---		N:A 1/1