







SPECIFICATIONS
Current Rating:0.75 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000MΩ Min
Contact Resistance:20mΩ Max
Operation Temperature:-40°to+105°
Insrlator Material:Polyester(UL94V-0)
Contact Material:Phosphor bronze
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp:240°C for30-60seconds
(260°C for5seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

P/N	PIN	DIM.A	DIM.B
JXT-PM1.0-2X2P-A2	2*1	0.00	1.00
JXT-PM1.0-2X4P-A2	2*2	1.00	2.00
JXT-PM1.0-2X6P-A2	2*3	2.00	3.00
JXT-PM1.0-2X8P-A2	2*4	3.00	4.00
JXT-PM1.0-2X10P-A2	2*5	4.00	5.00
JXT-PM1.0-2X12P-A2	2*6	5.00	6.00
JXT-PM1.0-2X14P-A2	2*7	6.00	7.00
JXT-PM1.0-2X16P-A2	2*8	7.00	8.00
JXT-PM1.0-2X18P-A2	2*9	8.00	9.00
.....			
JXT-PM1.0-2X80P-A2	2*40	(40-1)	40

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X ±0.30	X.* ±5°	PART NO.	TITLE: 1.0FH H2.0 2xNPin SMT	
.XX ±0.20	X.X* ±1°	JXT-PM1.0-2XNP-A2	W2.5 U 3.8 PB2.3 6T	
.XXX ±0.10	X.XX* ±0.5°	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		SCALE
MATERILA	---	APPD: Ava		SHEET
FINISH	---			N:A
				1/1