



Pushing Performance
Since 1945

D-Sub M 2W2C female straight PCT



Part number	09 69 110 9007
Specification	D-Sub M 2W2C female straight PCT

Identification

Category	Connectors
Series	D-Sub
Identification	Mixed
Element	Connector
Description of the contact	Straight

Version

Gender	Female
Size	D-Sub 1
Number of contacts	2
Number of signal contacts	0
Number of special contacts	2
Coding	With coding
Locking type	Fixing flange with feed through hole Ø 3.1 mm
Details	Please order special contacts separately.

Technical characteristics

Insulation resistance	> 5 x 10 ⁹ Ω
Limiting temperature	-55 ... +150 °C
Mating cycles	≥500
Test voltage U _{r.m.s.}	1 kV
Isolation group	II (400 ≤ CTI < 600)
Hot plugging	No



Pushing Performance
Since 1945

Material properties

Material (insert)	Thermoplastic resin (PCT) Shell: steel, tin plated
Colour (insert)	Light grey
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	100
Net weight	5.2 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140096554
ETIM	EC001136
eCl@ss	27440214 D-Sub coupler