









适用扁平线(Applicable Flat Cable)




SECTION A-A



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B	C	D
JXT-AFC05-AS4P-H20	4	1.50	2.56	7.60	5.20
JXT-AFC05-AS5P-H20	5	2.00	3.06	8.10	
JXT-AFC05-AS6P-H20	6	2.50	3.56	8.60	
JXT-AFC05-AS7P-H20	7	3.00	4.06	9.10	
JXT-AFC05-AS8P-H20	8	3.50	4.56	9.60	
JXT-AFC05-AS9P-H20	9	4.00	5.06	10.10	
JXT-AFC05-AS10P-H20	10	4.50	5.56	10.60	
JXT-AFC05-AS11P-H20	11	5.00	6.06	11.10	
JXT-AFC05-AS12P-H20	12	5.50	6.56	11.60	5.75
.....					
JXT-AFC05-AS34P-H20	34	16.50	17.56	22.60	
JXT-AFC05-AS35P-H20	35	17.00	18.06	23.10	
JXT-AFC05-AS36P-H20	36	17.50	18.56	23.60	
.....		...			
JXT-AFC05-AS60P-H20	60	(60-1)*0.5	(60+1)*0.5+0.06	(60+11)*0.5+0.1	



适用线路板(PCB LAYOUT)

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25°C~+85°C.
3. 额定电压: 50V, AC/DC.
4. 接触电阻: ≤0.03Ω.
5. 绝缘电阻: ≥500MΩ

序号	品名	材质
1	0.5拉拔胶芯(H2.0)	LCP UL94V-0 本色
2	0.5拉拔上端子(H2.0)	铜合金/表面镀锡
3	0.5拉拔卧式后盖(H2.0)	LCP UL94V-0 黑色
4	0.5拉拔焊片(H2.0)	铜合金/表面镀锡

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	.X'±5°	PART NO.	TITLE:		
.XX±0.20	.XX'±2°	JXT-AFC05-ASNP-H20	0.5 Pitch 拉拔卧式上接(H=2.0)		
.XXX±0.05	.XXX'±1°	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	---	APPD: Ava		N:A	1/1