







SECTION A-A




Applicable Flat Cable

技术指标:

1. 塑件表面应光洁, 无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
3. 额定电压: 50V, AC/DC(等效).
4. 接触电阻: $\leq 0.03\Omega$.
5. 绝缘电阻: $\geq 500M\Omega$

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B	C	D
JXT-AFC10-AS4P-H20	2	1.00	3.06	8.10	5.20
JXT-AFC10-AS5P-H20	3	2.00	4.06	9.10	
JXT-AFC10-AS6P-H20	4	3.00	5.06	10.10	
JXT-AFC10-AS7P-H20	5	4.00	6.06	11.10	
JXT-AFC10-AS8P-H20	6	5.00	7.06	12.10	
JXT-AFC10-AS9P-H20	7	6.00	8.06	13.10	
JXT-AFC10-AS10P-H20	8	7.00	9.06	14.10	
JXT-AFC10-AS11P-H20	9	8.00	10.06	15.10	
JXT-AFC10-AS12P-H20	10	9.00	11.06	16.10	
.....					
JXT-AFC10-AS16P-H20	16	15.00	17.06	22.10	5.75
JXT-AFC10-AS17P-H20	17	16.00	18.06	23.10	
JXT-AFC10-AS18P-H20	18	17.00	19.06	24.10	
.....		...			
JXT-AFC10-AS30P-H20	30	(30-1)*1.0	(30+1)*1.0+0.06	(30+6)*1.0+0.1	



适用线路板(PCB LAYOUT)

序号	品名	材质
1	1.0拉拔卧式胶芯(H2.0)	LCP UL94V-0 本色
2	1.0拉拔上接端子(H2.0)	铜合金/表面镀锡
3	1.0拉拔卧式后盖(H2.0)	LCP UL94V-0 黑色
4	1.0拉拔焊片(H2.0)	铜合金/表面镀锡

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	.X*±5°	PART NO.	TITLE:		
.XX±0.20	.XX*±2°	JXT-AFC10-ASNP-H20	1.0 Pitch 拉拔卧式上接 (H=2.0)		
.XXX±0.05	.XXX*±1°	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			
MATERILA	---	APPD: Ava			
FINISH	---			SCALE N:A	SHEET 1/1