












Part No	Pin	A	B	C
JXT-A05FC-S4FLZ-H20	4	1.50	2.60	7.60
JXT-A05FC-S5FLZ-H20	5	2.00	3.10	8.10
JXT-A05FC-S6FLZ-H20	6	2.50	3.60	8.60
JXT-A05FC-S7FLZ-H20	7	3.00	4.10	9.10
JXT-A05FC-S8FLZ-H20	8	3.50	4.60	9.60
JXT-A05FC-S9FLZ-H20	9	4.00	5.10	10.10
JXT-A05FC-S10FLZ-H20	10	4.50	5.60	10.60
JXT-A05FC-S11FLZ-H20	11	5.00	6.10	11.10
JXT-A05FC-S12FLZ-H20	12	5.50	6.60	11.60
JXT-A05FC-S13FLZ-H20	13	6.00	7.10	12.10
JXT-A05FC-S14FLZ-H20	14	6.50	7.60	12.60
JXT-A05FC-S15FLZ-H20	15	7.00	8.10	13.10
.....		...		
JXT-A05FC-S60FLZ-H20	60	(60-1)*0.5	(60+1)*0.5+0.1	(60+11)*0.5+0.1



序号	品名	材质
1	端子	磷青铜/表面镀锡
2	焊片	黄铜/表面镀锡
3	基座	LCP UL94V-0 本色
4	锁条	LCP UL94V-0 黑色

技术指标:

- 1.额定电流:0.5A
- 2.温度范围:-40~85℃
- 3.额定电压:50V,AC/DC(等效)
- 4.接触电阻:≤0.03Ω
- 5.绝缘电阻:≥500MΩ

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.15	X.*±5°	PART NO.	TITLE:		
X.X±0.10	X.X*±1°	JXT-A05FC-SNFLZ-H20	0.5-A全包拉拔式(正位)		
X.XX±0.15	X.XX*±0.5°	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	— — —	APPD: Ava		N:A	1/1
FINISH	— — —				