







REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SPECIFICATIONS

Current Rating: 1.0 Amps
Withstanding Voltage: AC 500V
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Operation Temperature: -40°to+105°
Insrlator Material: Polyester(UL94V-0)
Contact Material: Brass
Standard: PA6T
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
JXT-PZ1.27-1X1P-A1	1	0.00	1.27
JXT-PZ1.27-1X2P-A1	2	1.27	2.54
JXT-PZ1.27-1X3P-A1	3	2.54	3.81
JXT-PZ1.27-1X4P-A1	4	3.81	5.08
JXT-PZ1.27-1X5P-A1	5	5.08	6.35
JXT-PZ1.27-1X6P-A1	6	6.35	7.62
JXT-PZ1.27-1X7P-A1	7	7.62	8.89
JXT-PZ1.27-1X8P-A1	8	8.89	10.16
JXT-PZ1.27-1X9P-A1	9	10.16	11.43
.....			
JXT-PZ1.27-1X50P-A1	50	(50-1)x1.27	(50)x1.27

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X	±0.30	X.*	±5°	PART NO.
.XX	±0.20	X.X*	±1°	JXT-PZ1.27-1XNP-A1
.XXX	±0.10	X.XX*	±0.5°	DESIGN: Ethan
UNITS	mm	CHED: Olvia	MANUFACTURE DWG	
MATERILA	---	APPD: Ava	SCALE	SHEET
FINISH	---		N:A	1/1