

修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
A0		NEW RELEASE	黄艳兰	2021-05-10

Specifications:

Contact resistance: $\leq 20\text{m}\Omega$

Insulation resistance: $\geq 500\text{M}\Omega$

Rated voltage: 100V AC DC

Rated current: 2.0A AC DC

Withstand Voltage: 500V AC/minute

Temperature Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

Housing: PA66 UL94V-0, Natural

包装数量：2K/包

PIN.	DIM A	DIM B	DIM C	DIM D
2pin	1.50	5.00	3.60	2.70
3pin	3.00	6.30	5.10	3.45
4pin	4.50	7.80	6.60	4.45
5pin	6.00	9.30	8.10	4.45
6pin	7.50	10.80	9.60	7.45
7pin	9.00	12.30	11.10	7.45
8pin	10.50	13.80	12.60	9.80
9pin	12.00	15.30	14.10	9.80
10pin	13.50	16.80	15.60	9.80
11pin	15.00	18.30	17.10	9.80
12pin	16.50	19.80	18.60	9.80
13pin	18.00	21.30	20.10	11.30
14pin	19.50	22.80	21.60	11.30
15pin	21.00	24.30	23.10	11.30
16pin	21.00	25.80	24.60	11.30




深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co., LTD

电话：0755-27111216 传真：0755-29940187

-TOLERANCES-
UNLESS OTHERWISE SPECIFIED
公差参数表



TITLE:
产品名称： ZE1.5胶壳

X.X ± 0.30 X.X° $\pm 3^{\circ}$

APPD:
核准： 谢亮

PART NO:
产品编号： HDGC1501HD-XP

X.XX ± 0.30 X.XX° $\pm 2^{\circ}$

CHECK:
校对： 王建业

DATE SCALE UNIT CODE NUMBER

X.XXX ± 0.10 X.XXX° $\pm 1^{\circ}$

DRAW:
绘图： 黄艳兰

2021-05-10 1:1 mm A018