





序号	品名	材质
1	1.25 Pitch S/T Wire To Board Housing DIP(H=4.7)	PA66 UL94V-2 Yellow
2	1.25 Pitch S/T Wire To Board Terminal DIP(H=4.7)	Copper Alloy/ Tin Plating

Technical Index:


- 1.The surface of the plastic parts should be smooth,no rough edges,no obvious shrinkage,defects,cracks and other phenomena)
- 2.Lock Configuration: 2 to 3Pin is 1, ≥4Pin is 2
- 3.Temperature range: -25°C~+85°C.
- 4.Rated voltage: 125V, AC/DC.
- 5.Contact resistance: ≤0.02Ω.
- 6.Insulation resistance: ≥100MΩ



SECTION A-A

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B	C
JXT-MX1.25-2PZZ-H1	2	1.25	3.20	4.30
JXT-MX1.25-3PZZ-H1	3	2.50	4.45	5.55
JXT-MX1.25-4PZZ-H1	4	3.75	5.70	6.80
JXT-MX1.25-5PZZ-H1	5	5.00	6.95	8.05
JXT-MX1.25-6PZZ-H1	6	6.25	8.20	9.30
JXT-MX1.25-7PZZ-H1	7	7.50	9.45	10.55
JXT-MX1.25-8PZZ-H1	8	8.75	10.70	11.80
JXT-MX1.25-9PZZ-H1	9	10.00	11.95	13.05
JXT-MX1.25-10PZZ-H1	10	11.25	13.20	14.30
JXT-MX1.25-11PZZ-H1	11	12.50	14.45	15.55
JXT-MX1.25-12PZZ-H1	12	13.75	15.70	16.80
JXT-MX1.25-13PZZ-H1	13	15.00	16.95	18.05
JXT-MX1.25-14PZZ-H1	14	16.25	18.20	19.30
JXT-MX1.25-15PZZ-H1	15	17.50	19.45	20.55
JXT-MX1.25-16PZZ-H1	16	18.75	20.70	21.80
JXT-MX1.25-17PZZ-H1	17	20.00	21.95	23.05
JXT-MX1.25-18PZZ-H1	18	21.25	23.20	24.30
JXT-MX1.25-19PZZ-H1	19	22.50	24.45	25.55
JXT-MX1.25-20PZZ-H1	20	23.75	25.70	26.80



适用线路板(PCB LAYOUT)

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X:±0.35	X.X':±3"	PART NO. JXT-MX1.25-NPZZ-H1	TITLE: Socket-type terminal Vertical plug	
X.XX:±0.25	X.XX':±2"		DESIGN: Ethan	
X.XXX:±0.15	X.XXX':±2"		CHED: Olvia	
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG	
MATERILA	---	CHED: Olvia	 SCALE N:A	SHEET 1/1
FINISH	---	APPD: Ava		