





RoHS

目 录
MAPX设 变 内 容
MODIFICATION日 期
DATE

电气特性:Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗: Contact Resistance
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance:
1000MEGA ohms MIN

物理性能: Mechanical:

1. 插拔力: Connector Mate and Unmate Force
Mate force: 3.57kgf (MAX)
Unmate force: 0.7kgf (MIN)
2. 端子保持力: Terminal Retention
1.0kgf (MIN)
3. 寿命: 1500次

原材料: Material:

1. 塑胶: Housing: LCP
2. 端子: Contact: Copper Alloy C2680
3. 外壳: Shell: SPCC /C2680

电镀: Finish:

1. 端子 Contact: Au G/F u" Plated on contact area
Tin50u" Plated on solder area
Nickel 50u" Plated underplating over all.
2. 外壳 Shell: Nickel 50u" Min plating over all.

RBCOMMENDBD P.C.B PATTBRN LAYO UT

		产品图 PRODUCT CHART DWG		深圳市精拓金电子有限公司									
Pin NUMBER	SIGNAL NAME			单位 UNITS	MM	制图 DRAWING	L S S	产品料号 PRODUCT PART NO.	903-131A2023S10100				
1	VBUS	公差一览表 TOLERANCE UNLESS OTHERWISE		比例 SCALE	1:1	审核 CHKD	郭志富	产品名称 PRODUCT NO.	AF无后盖弯脚有边内弹 铁壳一型加宽LCP黑胶SMT				
2	D-	X.	±0.35								X".	±5"	
3	D+	.X	±0.30	.X"	±2"	日期 DATE	2015/10/20	核准 APPD	黄国荣	角法 VIEW		版本 VER	A0
4	GND	.XX	±0.25	.XX"	±1"								
		.XXX	±0.10	.XXX"	±0.5"								