



PCB LAYOUT

NOTES:

ELECTRICAL:

1. VOLTAGE RATING :125 VAC RMS.
2. CURRENT RATING :1.5 AMP.
3. CONTACT RESISTANCE :30 MILLIOHMS MAX.
4. INSULATION RESISTANCE :500 MEGOHMS MIN @ 500V DC .
5. DIELECTRIC STRENGTH :1000V AC RMS 50Hz. 1MIN.

MECHANICAL:

1. HOUSING MATERIAL :GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL :PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
3. PLATING :GOLD PLATING OVER NICKEL.
4. OPERATING :750 CYCLES MIN.
5. PCB RETENTION PRE-SOLDER :1 LB MIN.

ENVIRONMENTAL:

1. Temperature Range : $-45^{\circ}\text{C} \sim +85^{\circ}\text{C}$
2. Relative Humidity : $90 \sim 95\%$ ($40 \pm 2^{\circ}\text{C}$)



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X.' $\pm 2'$ X.X' $\pm 0.5'$	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: RJ11 1X2 6P6C 90 ° DIP全塑带耳	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW54-RJ11-130B	MOLD NO.
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2206181634	SHEET NO. 1 OF 1