




主要参数:

1. 额定电压. 电流: 125V/1.5A max
2. 接触电阻: 40m Ω Max 初始态 100 Ω Max 最终态
3. 绝缘电阻: 500M Ω Min
4. 试验条件: DC500V/5.0mA for 1 minute
5. 盐雾测试: 8±0.5H

e	LED	1		YELLOW	
d	LED	1		GREEN	
c	Shielding	1	Brass	Ni Plating	
f	COVER	1	LCP+15% G.F UL94V-0	BLACK	
b	Terminal	8	Phosphor Bronze	PLATING & COLOR	
a	Housing	1	LCP+15% G.F UL94V-0	BLACK	
NO.	PART NAME	Q'TY	MATERIAL	Material & Plating	Remark



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY :	DATE :	PART NAME:	
	陈一鸣	2014-02-23	RJ45 沉板SMT 带灯	
	CHECKED BY:	DATE :	PART NO.	HYCW163-RJ45-420B
	马跃	2014-02-23	MOLD NO.	
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY:	DATE :	DRAW NO:	HYC-RJ18121317
	邱敏	2014-02-23	SHEET NO.	1 OF 1