









ELECTRICAL
RATING:DC 12V 2A:
CONTACT RESISTANCE:30mΩ MAX(INITIAL)
100mΩ MAX(FINAL)
INSULATION RESISTANCE: 100 MΩ MIN.
DIELECTRIC WITHSTAND VOLTAGE: 500V AC
DURABILITY TEST: 5,000 CYCLES.
TEMPERATURE RANGE: -25°C TO +75°C
INSERTION FORCE:1.13kgf±40%
WITHDRAWAL FORCE:>1.0kgf
SALT SPRAY:48H
MATERIALS & PLATING: SEE THE TABLE BELOW.



3D VIEW



3D VIEW



环保
Green Product

5	基座	1	LCP UL94V-0	BLACK
4	插芯	1	H59 φ2.5	Ni Plating
3	静片	1	BRASS T=0.3	Sn Plating
2	动片	1	C5191 t=0.25mm	Sn Plating
1	插芯片	1	BRASS T=0.4	Sn Plating
NO.	PART NAME	QT'Y	MATERIAL	REMARK

							ANGLE	±2°	Designed:	Checked:	Approved:	Date:	MODEL TYPE:
							30 ~	±0.30				2017/09/20	DC POWER JACK
							10 ~ 30	±0.25					PART NO.
							~ 10	±0.15					CAX-DC-11S1T-2.5-XL
—	A/0		NEW	—	—	—							UNIT:
ECN NO	REV	DATE	DESCRIPTION	CHANGE	CHECK	APPRO.	UNSPECIFIED TOLERANCE						SCALE:
	1												VIEW:
	2												Edition:
	3												mm
	4												1:1
	5												⊕
	6												A/0
	7												
	8												
	9												
	10												

浙江创都电子科技有限公司

UNIT:	SCALE:	VIEW:	Edition:
mm	1:1	⊕	A/0