








PC Board Layout



A-A



PCB JACK Specification

1. Insulation Resistance: 500M Ω MIN @ 500 VDC
2. Withstanding Voltage: AC1000V 50Hz or 60Hz 1min.
3. Durability: 600 Mating Circles MIN.
4. Gold Plating: (3;6;15;30;50) μ inch
5. Tolerances Unless Otherwise Specified
.0 $\pm$ 0.25 .00 $\pm$ 0.20 .000 $\pm$ 0.10



深圳市华宇创精密电子有限公司

TOLERANCE: X.X $\pm$ 0.30 X.XX $\pm$ 0.25 X.XXX $\pm$ 0.15 X.' $\pm$ 2" X.X' $\pm$ 0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: RJ45 90° DIP 8P8C全塑带耳	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW251-RJ45-206B	MOLD NO.
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 柯南	DATE : 2014-02-23	DRAW NO: HYC-RJ19092118	SHEET NO. 1 OF 1