




REV	DESCRIPTION	DESIGN	DATE
A0	NEW RELEASE		2025/07/08


















PCB LAYOUT(Tolerance:±0.05)

SCALE:1/2



Specifications:

Contact resistance:≤10mΩ
Insulation resistance:≥1000MΩ
Rated voltage:250V AC DC
Rated current:5.0A AC DC
Withstand Voltage：1000V AC/minute
Temperature Range:−40℃～+125℃
Housing:LCP UL94V−0,BLACK
Contacts:Brass/MATTE Sn−plated
Solder Tabs:Brass/MATTE Sn−plated

PIN	DIM A	DIM B
2	3.00	9.65
3	6.00	12.65
4	9.00	15.65
5	12.00	18.65
6	15.00	21.65
7	18.00	24.65
8	21.00	27.65
*9	24.00	30.65
*10	27.00	33.65
*11	30.00	36.65
*12	33.00	39.65

ORDER INFORMATION:

A3006R-XP-F9KB3-R

- PART No.
- No.OF CIRCUITS: 02-12
- PLASTIC MATERIAL: F9K=LCP
- PLATING: B=MATTE Sn
- Metal code: 3=Brass
- PACKAGING: R=REEL

浙江创都电子科技有限公司

GENERAL TOLERANCE		USE: CUSTOMER
X. ±0.50	X. ±5°	APPD:
X.X ±0.30	X.X ±2°	CHKD:
X.XX ±0.20	X.XX ±1°	DR:
	UNITS: mm	

TITLE: MX3.0单排卧贴

PART NO.: CAX-MX3.0-D0**WB-XT

DWG NO.:

SCALE 1 : 1

SHEET 1 / 1