**Electrical Characteristics :**

Insulation Resistance : 500MΩ Min.

Contact Resistance : 50mΩ Max.

Withstand Voltage : 1000 VAC 1 minute.

Current Rating : 1.5A

Material:






Housing: Thermoplastic UL 94V-0

Contact : Selective Gold Plating

Terminal: 0.25mm Thickness Copper Alloy
Plated With Gold And Tin In Solder Area.

Shell: Alloy ,Nickel Plating

Fork:Alloy

W/LED RECOMMENDED PCB LAYOUT
COMPONENT SIDE(t=1.6mm, tol:±0.05)**LED ELECTRICAL CHARACTERISTIC**

Standard LED	Wavelength	Forward V (Min/Max)	Forward A	Type
Green	568nm	1.8V/2.8V	20mA	squareness
Yellow	585nm	1.8V/2.8V	20mA	squareness

**深圳市华宇创精密电子有限公司**

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: RJ45 90° DIP 沉板上4.3带灯	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW425-RJ45-430B
	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-2212022101
SCALE:1:1	SIZE: A4		SHEET NO.	1 OF 1