











工程變更通知單號 ECN NO.	更改 REV	設 變 內 容 MODIFICATION	日 期 DATE	製 圖 DRAW	核 准 APPROVE
	A1	NEW ISSUE	2016.07.02		



PCB LAYOUT TOP VIEW

PLUG VIEW



LEAD FREE

COVER	1	PA9T	BLACK
HOUSING	1	PA9T	BLACK
PIN	1	H59	Ni-Plated
TERMINAL	1	BRASS t=0.30	CuSn-Plated
TERMINAL	1	PHOSPHOR BRONZE t=0.25	CuSn-Plated
TERMINAL	1	BRASS t=0.35	CuSn-Plated

NO	DESCRIPTION	QTY	MATERIAL	REMARK
QC Inspection Item	DIMENSION IN mm [Inch]		浙江创都电子科技有限公司	
	TOLERANCE UNLESS OTHERWISE SPECIFIED		DWG NO.	FILE NO.
	X ±±0.5	X *±		
	X.X ±±0.3	X.X *±		
QC Inspection Item	TITLE		CUSTOMER COPY	
	DC POWER JACK			
	APPROVE JACK		DRAW JULY	PROJ. SCALE A:1
	CHECK ALAN			SHEET 1 / 1

SPECIFICATION

1. Rating : DC 20V 5.0A;
2. Contact resistance: $\leq 0.03 \Omega$;
3. Insulation resistance: $\geq 100M \Omega$ (DC500V);
4. Withstand voltage: 500VAC ;
5. Insertion and extraction force: 3-30N;
6. life test: 5,000 cycles.
7. Operating temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.

