








RECOMMENDED
PCB LAYOUT

SPECIFICATIONS:
Impedance: 75 Ohms
Frequency Range: DC~3G
VSWR: 1.3max
Working Voltage: 500V RMS @ SEA level
Insulation Resistance: 5000 Ohms min
Temperature Range: -55°C TO +155°C
Drawings products are in line with ROHS standards

NOTE:

Tolerance
X. ± 0.15
X X ± 0.10
X XX ± 0.05
Angular $\pm 5^\circ$

View
UNIT
MM

Name: BNC JACK CONNECTOR

Dosin Industrial (Hk) Co Ltd
东莞市松本五金电子有限公司
Dosin Hardware Electronics Co, Ltd
E-mail: dosin2005@163.com
dosin2005@dosin-china.com
Web: http://www.dosin.com
TEL: (0086) 769-81153906
FAX: (0086) 769-81878836

SIZE
A Product NO. DOSIN-801-0310

REV
A

Date/Time
2015/07/21

CAD FILE
H/company drawings/BD

SHEET: 1 OF 1

DOSIN — 316 CONSTRUCTION — Dosin Industrial (Hk) Co., Ltd 东莞市德索五金电子有限公司 Dosin Hardware Electronics Co., Ltd E-mail: dosin2006@163.com dosin2006@dosin-hk.com Web: http://www.dosinconn.com TEL: (0086) 769-81153906 FAX: (0086) 769-81878336										NAME: BNC JACK CONNECTOR SIZE A Product NO. DOSIN-801-0310 DATE: 2015/07/21 CAD FILE H/company drawings/3D REV A										
1 Body			BRASS			Gold:1-1.6u"			NOTE:											
2 Contact pin			BRASS			Gold:1-1.6u"														
3 Insulation			TPE/LV			None														
4									Tolerance											
5																				
6																				
7						DRAWN			View											
8						Zelin. Zhang														
9						CHECKED														
10									UNIT											
Component Number																				
Material																				
Finish									SCALE											
APPROVALS																				
A			B			C			D			E			F			G		