








PCB LAYOUT/TOP VIEW
TOLERANCE=±0.05



电气特性

1. 额定电压: 125 VAC RMS
2. 额定电流: 1.5 AMP
3. 接触电阻: 20 mΩ MAX
4. 绝缘电阻: 1000 MΩ MIN. @500 VDC
5. 耐压强度: 1000 V AC 或 1500V DC RMS @ 0.5mA 50 Hz 或 60 Hz 一分钟

环境特性

1. 储存温度: -40℃ ~ +85℃
相对湿度 < 80%
2. 工作温度: -40℃ ~ +85℃
- 波峰焊温度: 265 ± 5℃ 5"10S

机构特性:

1. 塑壳材质: LCP 黑色, UL94V-0
2. 扁针材质: C5191-H T=0.35 ± 0.01
3. 扁针电镀: 接触区镀金 +3u",
镍底 30-50u". 镀亮锡 100-120u".
4. 卡勾: C2680-EH T=0.35 ± 0.01.
电镀镍底 50-80u", 亮锡 100-120u"
5. 可靠性: 最少 750 次插拔;
6. 插入/拔出力: 30N MAX.
7. 配合强度: 50N 60S ± 5S.



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: RJ45 180 ° 8P8C SMT	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW157-RJ45-156B	MOLD NO.
	APPROVED BY: 邱国夷	DATE : 2014-02-23	DRAW NO: HYC-1508101456	SHEET NO. 1 OF 1
	SCALE:1:1	SIZE: A4		