




COLOR TABLE

CODE	A	B
COLOR	WHITE	RED

NOTES:

ELECTRICAL:

1:RATED CURRENT: 1A Max.

2:RATED VOLTAGE: 12V DC.

3:CONTACT RESISTANCE: 30 MILLIOHMS Max.

AFTER TESTING:100 MILLIOHMS Max.

4:INSULATION RESISTANCE: 100 MEGAOHMS Min.

5:DIELECTRIC WITHSTANDING VOLTAGE: 500 VAC Min.

MECHANICAL:

1:INSERTION FORCE: 3N-30N.

2:WITHDRAWAL FORCE: 3N-30N.


3:DURRABILITY: 500 CYCLES.

ENVIRONMENTAL:



TEMPERATURE RANGE: -20°C TO 60°C.

MARK "▼" AS THE KEY CONTROL SIZE.


PIN PIN POSITION SIZE IS SUBJECT TO PCB BOARD.



A向



SCHEMATIC

PCB LAYOUT
TOP VIEW

⑤	ERMINAL-B	1	BRASS t=0.5	CuSn PLATED	RoHS 2.0					
④	TERMINAL-A	2	BRASS t=0.5	CuSn PLATED						
③	WASHER	2	ABS	SEE COLOR TABLE						
②	SOCKET	2	BRASS t=0.36	CuSn PLATED						
①	HOUSE	1	ABS	BLACK						
NO.	PART NAME	Q'TY	MATERIAL	FINISH/COLOR	REMARK					
ANGLE		±5°	MODEL NAME: (PART NO.)		浙江创都电子科技有限公司					
63 < L		±0.5								
16 < L ≤ 63		±0.4								
4 < L ≤ 16		±0.3								
L ≤ 4		±0.2	TITLE: RCA PIN JACK							
TOL TABLE:		Q'TY: /								
		APPROVED: 04/03'24		UNIT: mm						
		04/03'24		VIEW: 						
		04/03'24		SCALE: 5:1						
		04/03'24		SHEET: 1/1						
		04/03'24		SIZE: A3						