







全铜

P. C. B Layout
(Copper-sided view)

SPECIFICATION

- 1.Rating : DC 24V 5.0A;
- 2.Contact resistance: $\leq 30m\Omega$;
- 3.Insulation resistance: $\geq 100M\Omega$ (DC500V);
- 4.Withstand voltage: 500VAC ;
- 5.Insertion and extraction force: 3-30N;
- 6.life test: 5,000 cycles;
- 7.Operation temperature range:-25℃~70℃;
- 8.Preservative temperature range:-30℃~75℃;
- 9.Sign"▲ "is importance dimension.

⑥	Shunt terminal	☒	1	BRASS t0.3	CuSn plating
⑤	Tip spring	☒	1	C5191 t0.25	CuSn plating
④	Center pin terminal	☐	1	BRASS t0.35	CuSn plating
③	Center pin	☐	1	H59	Nickel plating
②	Cover		1	PBT	Black
①	Housing		1	PBT	Black
NO.	DESCRIPTION		QTY	MATERIAL	REMARK

ECN NO	REV	DATE	DESCRIPTION	CHANGE.	CHECK.	APPRO.	UNSPECIFIED TOLERANCE
—	A/0		NEW	—	—	—	~ 10

ANGLE	±5°
30 ~	±0.30
10 ~ 30	±0.25
~ 10	±0.20

Designed:

Checked:

Approved:

Date:

2014/08/28

MODEL TYPE:

DC JACK

浙江创都电子科技有限公司

PART NO.

CAX-DC-005-5A-2.5T-XL

UNIT:

SCALE:

VIEW:

Edition:

mm

1:1

A/0