





REV.	ECN NO.	MODIFIED MARK	APPROVED
B		FIRST RELEASE	




PCB LAYOUT
TOP VIEW



COLOR TABLE

CODE	A	B	C
COLOR	WHITE	WHITE	WHITE
CODE	D	E	F
COLOR	RED	RED	RED



SCHEMATIC

NOTES:
ELECTRICAL:
1:RATED CURRENT: 1A Max.
2:RATED VOLTAGE: 12V AC.
3:CONTACT RESISTANCE: 30 MILLIOHMS Max.
AFTER TESTING:100 MILLIOHMS Max.
4:INSULATION RESISTANCE: 100 MEGAOHMS Min.
5:DIELECTRIC WITHSTANDING VOLTAGE: 500 VAC Min.
MECHANICAL:
1:INSERTION FORCE: 3N-30N.
2:WITHDRAWAL FORCE: 3N-30N.
3:DURRABILITY: 500 CYCLES.
ENVIRONMENTAL:
TEMPERATURE RANGE: -20°C TO 60°C.
MARK"▼"AS THE KEY CONTROL SIZE.
PIN POSITION AND SIZE OK IF FIT PCB BOARD

⑥	TERMINAL-B	3	BRASS t=0.35	CuSn PLATED	RoHS 2.0				
⑤	TERMINAL-A	3	BRASS t=0.35	CuSn PLATED					
④	SOCKET	3	BRASS	CuSn PLATED					
③	COVER	3	ABS	BLACK					
②	WASHER	6	PBT	SEE COLOR TABLE					
①	HOUSE	1	PBT	RED					
NO.	PART NAME		Q'TY	MATERIAL	FINISH/COLOR	REMARK			
ANGLE		±5°	MODEL NAME: (PART NO.)		浙江创都电子科技有限公司				
63 < L		±0.5							
16 < L ≤ 63		±0.4							
4 < L ≤ 16		±0.3							
L ≤ 4		±0.2	MAT'L: See table	DESIGN: 12/19'23	TITLE: RCA PIN JACK				
TOL TABLE:			FINISH: See table	CHECKED: 12/19'23	DWG NO.:CAX-AV-613-WR-HP		REV.: B		
			Q'TY:/	APPROVED: 12/19'23	UNIT: mm	VIEW: 	SCALE: 5:1	SHEET: 1/1	SIZE: A3