





REV.	ECN NO.	MODIFIED MARK	APPROVED
A		FIRST RELEASE	



NOTES:
ELECTRICAL:
1:RATED CURRENT: 0.3A Max.
2:RATED VOLTAGE: 50V DC.
3:CONTACT RESISTANCE: 30 MILLIOHMS Max.
AFTER TESTING:100 MILLIOHMS Max.
4:INSULATION RESISTANCE: 100 MEGAOHMS Min.
5:DIELECTRIC WITHSTANDING VOLTAGE: 500 VAC Min.
MECHANICAL:
1:INSERTION FORCE: 3N-30N.
2:WITHDRAWAL FORCE: 3N-30N.
3:DURRABILITY: 500 CYCLES.
ENVIRONMENTAL:
TEMPERATURE RANGE: -20°C TO 70°C.
MARK "▼" AS THE KEY CONTROL SIZE.
PIN POSITION AND SIZE OK IF FIT PCB BOARD.

COLOR TABLE

CODE	A	B	C
COLOR	BLACK	RED	WHITE

⑤	SOCKET	3	BRASS t=0.4	Au PLATING	RoHS2.0				
④	TERMINAL-A	3	BRASS t=0.3	CuSn PLATING					
③	COVER	1	ABS	BLACK					
②	WASHER	3	PBT	SEE COLOR TABLE					
①	HOUSE	1	PBT	BLACK					
NO.	PART NAME		Q'TY	MATERIAL	FINISH/COLOR	REMARK			
ANGLE		±5°	MODEL NAME: (PART NO.) AV-314-RWY		浙江创都电子科技有限公司				
63 < L		±0.5							
16 < L ≤ 63		±0.4							
4 < L ≤ 16		±0.3							
L ≤ 4		±0.2	MAT'L: See table	DESIGN:	TITLE: CAX-AV-314-RWY-PHP				
TOL TABLE:			FINISH: See table	CHECKED:	DWG NO.: CAX-AV-314-RWY-PHP	REV.: A			
			Q'TY: /	APPROVED: X	UNIT: mm	VIEW: 	SCALE: 5:1	SHEET: 1/1	SIZE: A3