







Function choice:
功能选择:

NO.	specification 产品规格	function 功能
01	MTS102/D2	SPDT: ON - ON
02	MTS112/D2	SPDT: ON - (ON)
03	MTS103/D2	SPDT: ON- OFF -ON
04	MTS113/D2	SPDT: (ON)-OFF- ON
05	MTS123/D2	SPDT: (ON)-OFF- (ON)

Specification(技术要求):

- Rated Load(额定负载): 2A 250VAC; 5A 125VAC
- Temperature Range(操作温度): -25℃--+85℃
- Contact Resistance(接触电阻): $\leq 0.02 \Omega$
- Insulation Resistance(绝缘电阻): $\geq 1000M \Omega$
- Withstand Voltage(耐压): AC1500V/min
- Operating Force(操作力): 2--15N
- Life(寿命): 10000 times
- material(材料): 胶木 and Cu/Ep Ag(黄铜镀银)

01	--	第一次出图			2024. 11. 14
版次 (REV.)	参考 (REF.)	描述 (DESCRIPTION)			日期 (DATE)
名称 (NAME)	Toggle Switch Specifications(钮子开关规格书)			绘图 (DRAW BY)	批核 (APP. BY)
型号 (MODEL NO.)	MTS Series CAX-MTS1**-D2-*JL			日期 (DATE)	日期 (DATE)
物料编号 (Material No.)	MTS102 D2	比例 (SCALE)	NTS(见标注)	日期 (DATE)	日期 (DATE)
公差除特别要求外, 均按此规定执行: X. =±0. 20, . X=±0. 15, . XX=±0. 1, <=±1°, 单位:mm (Tolerance unless otherwise specified: X. =±0. 20, . X=±0. 15, . XX=±0. 10, <=±1°, unit:mm)					

浙江创都电子科技有限公司