








SPECIFICATION

- 1.Rating : DC 20V, 4A;
- 2.Contact resistance: 30mΩ MAX;
- 3.Insulation resistance: 100MΩ MIN.;
- 4.Withstand voltage: 500VAC ;
- 5.Insertion and extraction force: 5-20N
- 6.life test: 5,000 cycles.
- 7.Salt spray test : 48H

MATING PLUG
P/N.: DP350135-0120-60000H

NO.	DESCRIPTION	QTY	MATERIAL	PLATING
D	PIN	1	HB i59	Au 0.8u"/Ni 40u"
C	CURVE PIECE	1	SUS 304	Ni 40u"
B	SPRING	1	C5191	Sn 80u"/Ni 40u"
A	HOUSING	1	PA46 BLACK 3A4	

REV.	ECN NO.	DESCRIPTION	DESIGN	DATE
A5	EC21101401	增加电镀膜厚描述 1A5	Tony	2021.10.14
A4	EC21082301	增加中心针保持力 3A4	Tony	2021.8.9
A3	EC21080901	中心针增加防转结构 1A3	Tony	2021.8.9

UNLESS OTHERWISE SPECIFIED TOLERANCES				浙江创都电子科技有限公司			
DECIMALS:		ANGLES:		DESIGN:	Tony	PART NAME:	
DIM	TOL	DIM	TOL	CHECK:	2021.10.14	Ø3.50X1.35	
X.	±0.50	X.	±2°		DC POWER JACK		
X.X	±0.30	X.X	±1°		PART NO.		
X.XX	±0.20	X.XX	——		CAX-DC-0830-4A-1.3-AU-XL		
X.XXX	±0.10	X.XXX	——	APPROVED	Andy	SHEET: 1/1 REV.: A5	
		UNIT: mm		2021.10.14	DRAWING NO		