










PCB LAYOUT
TOP VIEW (TOLERANCE: ± 0.05)



SCHEMATIC



技术特性:

使用条件: $-30 \sim 70^{\circ}$
额定负荷: DC30V 3A
接触电阻: $\leq 0.03 \Omega$
绝缘电阻: $\geq 100M \Omega$ DC250V
耐压: AC500V (50Hz) /min
插拔力: 3~20N
寿命: 5000次

6	弯片	1	H62黄铜带(Y) $\delta=0.30mm$	铜锡
5	插针	1	H65黄铜棒	铜锡
4	后盖	1	PBT	黑
3	平片	1	H62黄铜带(Y) $\delta=0.30mm$	铜锡
2	簧片	1	H65磷铜带 $\delta=0.25$	铜锡
1	基座	1	PBT	黄白红
序号	名称	数量	材料	备注

GENERAL TOLERANCES			
0.X	± 0.30	X°	$\pm 3^{\circ}$
0.XX	± 0.20		
0.XXX	± 0.10	X.X°	$\pm 1^{\circ}$
UNIT	SIZE	SCALE	
MM	A4	1:1	

DRAWN		C	TITLE: 电源插座	
DESIGN			PART NO.	
CHECKED			PRODUCT NO.	CAX-DC-005-**-CU-**-AP
APPROVED			DRAWING NO.	
UNIT: mm SCALE: 1:1 REV: 01-1 SHT: 1 OF 1				

浙江创都电子科技有限公司

ECN NO.	REV	DATE	DESCRIPTION	MDF'D	APP'D
	01	2021.12.22	NEW DRAWING RELEASE		