





REV	DESCRIPTION	DESIGN	DATE
A0	NEW RELEASE	陈亭伦	2025/07/08



Specifications:
Contact resistance:≤10mΩ
Insulation resistance:≥1000MΩ
Rated voltage:250V AC DC
Rated current:5.0A AC DC
Withstand Voltage: 1000V AC/minute
Temperature Range:-40℃~+125℃
Housing:LCP UL94V-0,BLACK
Contacts:Brass/MATTE Sn-plated
Solder Tabs:Brass/MATTE Sn-plated
CAP:Stainless steel

ORDER INFORMATION:

A3005V-XP-F9KB3-R-X

PART No.

No.OF CIRCUITS:

02P-12P

PLASTIC MATERIAL:

F9K=LCP

X:CAP

PACKAGING:




R=REEL

Metal code:

J=Brass

PLATING:

B=MATTE Sn



PIN	DIM	ADIM	B
2	3.00	9.65	
3	6.00	12.65	
4	9.00	15.65	
5	12.00	18.65	
6	15.00	21.65	
7	18.00	24.65	
8	21.00	27.65	
*9	24.00	30.65	
*10	27.00	33.65	
*11	30.00	36.65	
*12	33.00	39.65	

浙江创都电子科技有限公司

GENERAL

TOLERANCE

USE:

CUSTOMER

APPD:

CHKD:

DR:

UNITS:

mm

TITLE: MX3.0单排立贴

PART NO.: CAX-MX3.0-DO**LA-XT

DWG NO.:

SCALE

1 : 1

SHEET

1 / 1