




TYPE 1

TYPE 2

技术要求:

- 1) 材质: 见附表;
- 2) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;

GENERAL TOLERANCES		
DIM	TOL	DEG
X		±3.00°
X.X	±0.35	±2.00°
X.XX	±0.25	±1.00°
X.XXX	±0.15	

REV.	EC#	DESCRIPTION	DATE	DRAWN	CHECK	APPROVED
1.00		初版	2018-04-22			

15	71.12	76.2
14	66.04	71.12
13	60.96	66.04
12	55.88	60.96
11	50.8	55.88
10	45.72	50.8
9	40.64	45.72
8	35.56	40.64
7	30.48	35.56
6	25.4	30.48
5	20.32	25.4
4	15.24	20.32
3	10.16	15.24
2	5.08	10.16
Pin	A	B

- 1.工作温度: -25°C~+85°C.
- 2.适用线规: AWG#22~#18.
- 3.额定电压: 250V DC/AC(rms).
- 4.额定电流: 7A.
- 5.接触电阻: <0.01Ω
- 6.耐压值: 1500V AC/minute.
- 7.绝缘电阻: ≥1000MΩ.

3	FITTING NAIL	2 PCS	
2	PIN	n PCS	
1	Housing	1 PCS	材质: PA66 (UL94V-2), 颜色: 本色
NO.	NAME	Q'TY	DESCRIPTION



深圳市韩下电子有限公司

DRAW :	黄彬	2018-04-22	TITLE:	压线端子胶壳	DRAWNAME:	HX-CH5.08-3Y
DESIGN:			SERIES:	5.08 SERIES	DRAWNO.	
CHECK:	张伟	2018-04-22	P/N:		UNIT:	SHEET:
APPROVED	罗小春	2018-04-22	REV. 1.00	SCALE N/A	mm	1/1
CUSTOMER DRAWING						