






SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material:Nylon66, UL94V-0
- 8、Applicable Wires :AWG 26#~22#



编 号	尺寸 (mm)	
	A	B
A2506-02Y	2.50	7.40
A2506-03Y	5.00	9.90
A2506-04Y	7.50	12.40
A2506-05Y	10.00	14.90
A2506-06Y	12.50	17.40
A2506-07Y	15.00	19.90
A2506-08Y	17.50	22.40
A2506-09Y	20.00	24.90
A2506-10Y	22.50	27.40
A2506-11Y	25.00	29.90
A2506-12Y	27.50	32.40
A2506-20Y	47.50	52.40

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENE RL TOLERANCE		制 图 DRAWING	黄彬 2020、01、09		料 号 PART NO.	HX-5264-5Y		版 本 REV.	A
			X.±0.25	X.*±2°								
			.X±0.20	.X*±1°	审 核 CHECK	张伟 2020、01、10		品 名 TITLE	5264孔座		页 次 SHEET	1/1
			.XX±0.15	.XX*±0.5°	核 准 APPROVAL	罗小春 2020、01、10		客户料号 CUTM. NO.				
			.XXX±0.10	.XXX*±0.5°	单 位 UNITS	MM	比 例 SCALE	1:1	深圳市韩下电子有限公司			